


# Beverage Connecting Solutions

## Benefits

- Economical
- Uniform compression
- Quick and easy to install
- Slim, lightweight, yet strong



## SEALING SOLUTIONS

Applicable beverage applications: beverage dispensing systems, frozen beverage systems, hot beverage systems, soft drink systems, beer systems, home brew kits, syrup pumps, ice machines, beer pumps, ice makers, and bag-in-box connections



### StepLess® Ear Clamps 167

167 stainless steel  
6.5 – 120.5 mm

- **Narrow band:** concentrates transmission of clamping force
- **360° StepLess®:** uniform compression and uniform surface pressure



### 2-Ear Clamps 151

151 stainless steel  
4.1 – 46.0 mm

- **2-Ear version:** extended clamping range
- **Compact one-piece clamp:** for robust, secure connections
- **Clamp ear:** fast and simple installation



### Worm Drive Clamps 177 SAE Type “F”

177 stainless steel  
10.0 – 178.0 mm

- **Conforms to SAE J1508 Type “F”:** perforated band, large clamping range



### Beverage Clamp Kit

Item No. 18500075

Kit contains various sizes of StepLess® Ear Clamps 167 and one installation pincer.

## BEVERAGE | TOOLS FOR INSTALLATION

### Installation

For proper installation of clamps, use Genuine Oetiker Installation tools for best clamp performance.

1. Position the clamp on the hose/application
2. Align the jaw tips of the Oetiker installation tool with the ear of the clamp
3. Squeeze the ear



with Standard Jaw



with Side Jaw

### HAND INSTALLATION PINCERS (HIP)



#### Compound Action\* Standard Jaw Pincer

Oetiker HIP 2000 | 386  
Item no. 14100386

- Use where radial access to clamp is not restricted



#### Compound Action\* Side Jaw Pincer

Oetiker HIP 2000 | 387  
Item no. 14100387

- Dual purpose side jaw design
- Can be used in parallel or perpendicular position
- Install or remove clamps in confined areas

#### \*Key advantages of Compound Action Pincers

- Exclusive compound action for easier clamp installation and removal
- Designed and manufactured specifically to install and remove 5, 7, and 9 mm wide Genuine Oetiker ear clamps
- Optimized for professional medium and heavy duty use
- Generate up to 20% higher clamp sealing performance on genuine Oetiker clamps than other tools
- Better single handed use in confined areas
- Slip resistant grips for control and comfort
- Patent pending design
- Made in USA

### PNEUMATIC AND CORDLESS PINCERS



#### Pneumatic Pincers

Oetiker HO ME 2000

- Installation tool with high process reliability
- High-quality, complete pincer system for uniform clamp closures



#### Cordless Pincers

For Ear Clamps  
Oetiker Cordless Pincer CP 10

- Efficient, uniform and repeatable assembly
- Lightweight, ergonomic design

### ACCESSORIES - CUTTERS



#### Hand Clamp Cutter

Oetiker HCC 2000 | 407  
Item no. 14100407

- Quick and easy ear clamp cutting
- Safest method of clamp removal



#### Hand Tubing Cutter

Oetiker HTC 500 | 408  
Item no. 14100408

- Quickly cuts poly tubing up to 7/8" OD
- V-shaped notch keeps pipe or tube steady
- Light and durable glass filled nylon construction
- Super sharp blade for quick and easy cuts

**United States:** Oetiker, Inc. | 6317 Euclid Street  
Marlette, Michigan 48453 | T +1 800 959 0398  
Info.us.marlette@oetiker.com

**Efficient. Reliable. Secure.**

**Canada:** Oetiker Limited | 203 Dufferin Street South  
Alliston, Ontario L9R 1W7 | T +1 705 435 4394  
Info.ca.alliston@oetiker.com

[www.oetiker.com](http://www.oetiker.com)